

SWECO®

SANISEP PLUS™

FOR CONTAMINANT SENSITIVE APPLICATIONS

From checking incoming raw materials to safety screening in final packaging, the SWECO® SaniSep Plus™ insures manufacturers the most sanitary separation possible. The SaniSep Plus is engineered for use in pharmaceutical, food, dairy and other cross-contaminant, sensitive applications. With a crevice-free interior and streamlined exterior, the SaniSep is designed and manufactured to CGMP standards and meets the requirements of 3A, USDA, ASTM and FDA applications.

Constructed of polished stainless steel, the SaniSep Plus's Vortex™ Frame allows for the minimization of product build-up with flush connections, radius corner spouts, and continuous seam welds while enabling virtually complete product discharge.

SaniSep Plus can be customized with a variety of materials and surface finishes, in-place cleaning capability, screen cleaning/deblinding devices and portable or stationary stands.

SaniSep Plus units are available in 24", 30", 40" and 48" sanitary base and low profile designs.



*Low Profile SaniSep Plus
with optional mobile stand*

THE VORTEX™ FRAME IS DESIGNED
TO MINIMIZE THE PRODUCT BUILD-UP
BETWEEN THE SCREEN AND FRAME




We Put Technology In Motion™

www.sweco.com

SWECO HEADQUARTERS, P.O. Box 1509, 8029 Dixie Highway, Florence, KY 41022-1509: +1 (859) 371.4360 Fax: +1(859) 283.8469
SWECO MACON, 2919 Joycliff Road, Macon, GA 31211-2805: +1 (478) 745.5419 Fax: +1 (478) 741.1394
SWECO EUROPE S.A., Rue de la Recherche, 8, Parc Industriel Sud-Zone I, B-1400 Nivelles, Belgium: +32-67-893434 Fax: +32.67.214368
SWECO ASIA, 63 Hillview Ave. #03-02, Lam Soon Industrial Building, Singapore 669569:+65.6762.1167 Fax: +65.6762.1313
SWEQUIPOS S.A. DE C.V., Aut. Mex-Qro, #2500 Km. 23.2, Tlalnepantla, Edo. Mexico: +52 (5) 390-07-32, Fax: +52 (5) 565-98-18

No Gap - No Problem Hygienically Engineered



The SaniSep Plus "No-Gap" design prevents product from getting trapped between the frame and the edge of the screen. When the product gets trapped, build-up occurs, contributing to contamination and other unsanitary conditions. The screen ring is designed to be outside the separation chamber, yielding a crevice-free interior.



SaniSep Plus Vortex™ Frame



The unique Vortex™ Frame design is engineered to minimize the gap between the screen and the frame, virtually eliminating product build-up.

Features

- Designed for contaminant sensitive applications
- Crevice-free interior
- Streamlined exterior
- Optional over-center-clamping system
- "No-gap" design
- Radius cornered spouts
- Continuous seam welds
- Three drive packages
 - Sanitary Base
 - Single Motor Low Profile
 - Dual Motor Low Profile
- Optional stainless steel motors for Low Profile drive

Available Industry Specifications



We Put Technology In Motion™
e-mail: info@sweco.com

